




## On-Q 14-inch Enclosure, No Cover

Part No. EN1480



This 14" enclosure features universal On-Q bay-style mounting holes that are compatible with all bay-style modules. It also includes larger top openings that make pulling wire easier as well as additional knockouts, more side lances, and side tabs for



### Features & Benefits

Includes five openings on the top of the enclosure with knockouts

Drywall depth indicators

Flush and surface installation

Mounting tabs provide correct flush-mount position for standard installations

Patented mounting system offers versatile module mounting options

Made in the USA

### Specifications

#### General Info

Product Line	On-Q	Color	White
UPC Number	804428023050	Country Of Origin	United States
Application Sector	Residential	Standard	UL (UL985, UL1023, UL1863), cULus, CSA, RoHS
Type	Enclosure		

#### Dimensions

Product Width US	14.25 in	Product Depth US	3.6 in
Product Height US	14.0 in		

#### Listing Agencies / 3rd Party Agencies

---

CSA Listed

Yes

cULus Listed

Yes

---

**Additional Information**

---

RoHS Compliant

Yes

---

**Technical Information**

---

Thickness

0.1 in

Frame

Cold Rolled Steel

---