




**On-Q**  
**20-inch Enclosure, No Cover**  
Part No. EN2080



This 20" enclosure features universal On-Q bay-style mounting holes that are compatible with all bay-style modules. It also includes larger top openings that make pulling wire easier as well as additional knockouts, more side lances, and side tabs for

## Features & Benefits

Includes five openings on the top of the enclosure with knockouts

Drywall depth indicators

Flush and surface installation

Mounting tabs provide correct flush-mount position for standard installations

Patented mounting system offers versatile module mounting options

Literature pouch included for dealer information

Includes self-adhesive cable identification table

Made in the USA

## Specifications

### General Info

Product Line	On-Q	Color	White
UPC Number	804428023104	Country Of Origin	United States
Application Sector	Residential	Standard	UL (UL985, UL1023, UL1863), cULus, CSA, RoHS
Type	Enclosure		

### Dimensions

Product Width US	14.25 in	Product Depth US	3.6 in
Product Height US	20.0 in		

### Listing Agencies / 3rd Party Agencies

---

CSA Listed

Yes

cULus Listed

Yes

---

### Additional Information

---

RoHS Compliant

Yes

---

### Technical Information

---

Thickness

0.1 in

Frame

Cold Rolled Steel

---