



**On-Q**  
**28-inch Enclosure with Screw-On Cover**  
Part No. EN2800



This 28" enclosure is the perfect solution for a basic structured wiring system. It features larger top openings that make pulling wire easier as well as additional knockouts, more side lances, and side tabs for more flexible mounting. It includes a sc

## Features & Benefits

28-in Enclosure with Screw-On Cover

Drywall depth indicators

Flush and surface installation

Mounting tabs provide correct flush-mount position for standard installations

Patented mounting system offers versatile module mounting options

Literature pouch included for dealer information

Includes self-adhesive cable identification table

Cover included

Made in the USA

## Specifications

### General Info

Product Line	On-Q	Color	White
UPC Number	804428023111	Country Of Origin	United States
Application Sector	Residential	Standard	UL (UL985, UL1023, UL1863), cULus, CSA, RoHS
Type	Enclosure		

### Dimensions

Product Width US	14.25 in	Product Depth US	3.6 in
Product Height US	28.0 in		

---

## Listing Agencies / 3rd Party Agencies

---

CSA Listed	Yes	cULus Listed	Yes
------------	-----	--------------	-----

---

## Additional Information

---

RoHS Compliant	Yes
----------------	-----

---

## Technical Information

---

Thickness	0.1 in	Cable Entry	{2} rectangular knockouts for 1-gang electrical box
-----------	--------	-------------	---

---

Frame	Cold Rolled Steel
-------	-------------------

---