



On-Q
9-inch Dual-Purpose In-Wall Enclosure
Part No. ENP0900NA



The 9-inch Dual-Purpose In-Wall Enclosure is engineered to provide storage of structured wiring and AV components. The ENP0900NA is constructed of Wi-Fi transparent material to manage wireless components and AV devices at point-of-use locations, like directly behind a TV or other media centers. It can also be used for structured wiring purposes, such as networking equipment, access points, switches and more. The ENP0900NA is compatible with devices like Apple TV, Roku, Amazon Fire TV, small network switches and more. Includes cover, trim ring and drywall clips, allowing for both new construction and retrofit installations.

Features & Benefits

Designed for in-wall storage and distribution of structured wiring and AV components

Can be placed behind most TV wall-mounts including SANUS premium TV mounts

Compatible with devices like Apple TV, Roku, Amazon Fire TV, network switches, 3rd party structured wiring components and more

Trim ring conceals drywall cut out for clean finish and smooth transition to wall surface

Tool-free cover is low profile and designed to snap into place providing a "flush" appearance to wall surface

Knockout configurations support conduit and in-wall wired connections, while a cable pass through on cover allows for outside cable connections

Features (2) AC knockouts to accommodate a single gang junction box to power devices in enclosure

Universal mounting grid maximizes compatibility with 3rd party devices without additional mounting brackets

Features drywall clips to allow both retrofit and new construction installations

UL Listed and constructed of Wi-Fi transparent ABS plastic to ensure uninterrupted performance of wireless devices

Proudly made in the USA

Specifications

General Info

Product Line	On-Q	Color	White
Finish	Matte	UPC Number	804428434542
Country Of Origin	United States	Application Sector	Commercial, Residential
Standard	RoHS, UL, cULus	Type	Enclosure

Dimensions

Product Width US	14.37 in	Product Depth US	3.88 in
------------------	----------	------------------	---------

Product Height US	9.33 in
-------------------	---------

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Compatibility	Paintable with Rust-Oleum paint for plastic or equivalent	Seismic Tested	No
---------------	---	----------------	----

Thickness	0.1 in	Enclosure Type	Dual Purpose
-----------	--------	----------------	--------------

Frame	Injection-molded plastic	Mounting	Consult the Factory for Mounting Recommendations
-------	--------------------------	----------	--

Environmental Conditions	0 to 93% (relative humidity, non-condensing)
--------------------------	--
