



Ortronics
EZ Patch™ Box, CAT5E 5ft, Yellow, Qty 50
Part No. EZC5E05Q50-04



EZ Patch 50 pack, Clarity 5E Premium Category 5e modular patch cord, yellow, 5', four-pair UTP stranded 24 AWG PVC/CM, center tuned with Clarity 5E connecting hardware for optimum Category 5e installed performance

Features & Benefits

Dispenses patch cords quickly and easily: Reduces staging and installation time

Eliminates trash from opening bags: A green, friendly approach to packaging patch cords

Provides a more orderly staging approach: Eliminates errors and tangles from traditional staging

Factory Tested and ETL third party tested and verified to TIA/EIA 568C.2

Par align 2 pair-positioning technology: Maintains pair integrity through the plug termination, allowing mating hardware to be designed/tuned to these cords

Snagless plug design: Protects plugs when pulling through pathways or cable managers

Premium conductor cordage: Reliable performance and durable cord life

Specifications

General Info

Product Line	Ortronics	Color	Yellow
UPC Number	662875897613	Country Of Origin	Mexico
Application Sector	Commercial, Industrial	Warranty Type	5-Year
Type	Copper Patch Cord		

Dimensions

Product Width US	12.25 in	Product Depth US	12.25 in
Product Height US	12.5 in	Cable Length	5 ft

Additional Information

RoHS Compliant	Yes	Product Environmental Profile	Yes
----------------	-----	-------------------------------	-----

Technical Information

Jacket Material	PVC	Operating Temperature Min	-10 °C
-----------------	-----	---------------------------	--------

Category Performance Rating	Cat5e	Wire Gauge	24 AWG
-----------------------------	-------	------------	--------

Storage Humidity	0-90% RH (Non-Condensing)	Plating Specification	50 µ in Gold
------------------	---------------------------	-----------------------	--------------

Jacket Application	Riser Rated	Bend Radius	0.86 in
--------------------	-------------	-------------	---------

Shielded/Unshielded	Unshielded	Termination Style	Pre-Terminated
---------------------	------------	-------------------	----------------

Conductor Stranding	Stranded	Operating Temperature Max	60 °C
---------------------	----------	---------------------------	-------

Jacket Rating	CM Rated	Cable Diameter	0.215 in
---------------	----------	----------------	----------

Braid	Non-braided Wiring	Operating Temperature	-10°-60°C
-------	--------------------	-----------------------	-----------

Operating Humidity	0-90% RH (Non-Condensing)	Conductor Material	Copper
--------------------	---------------------------	--------------------	--------

Voltage	300.0 V	Storage Temperature	-40° - 60° C
---------	---------	---------------------	--------------
