



Ortronics
EZ Patch™ Box, CAT5E 5ft, Gray, Qty 50
Part No. EZC5E05Q50-08



EZ Patch 50 pack, Clarity 5E Premium Category 5e modular patch cord, gray, 5', four-pair UTP stranded 24 AWG PVC/CM, center tuned with Clarity 5E connecting hardware for optimum Category 5e installed performance

Features & Benefits

Dispenses patch cords quickly and easily: Reduces staging and installation time

Eliminates trash from opening bags: A green, friendly approach to packaging patch cords

Provides a more orderly staging approach: Eliminates errors and tangles from traditional staging

Factory Tested and ETL third party tested and verified to TIA/EIA 568C.2

Par align 2 pair-positioning technology: Maintains pair integrity through the plug termination, allowing mating hardware to be designed/tuned to these cords

Snagless plug design: Protects plugs when pulling through pathways or cable managers

Premium conductor cordage: Reliable performance and durable cord life

Specifications

General Info

| | | | |
|--------------------|------------------------|-------------------|--------|
| Product Line | Ortronics | Color | Gray |
| UPC Number | 662875897644 | Country Of Origin | Mexico |
| Application Sector | Commercial, Industrial | Warranty Type | 5-Year |
| Type | Copper Patch Cord | | |

Dimensions

| | | | |
|-------------------|----------|------------------|----------|
| Product Width US | 12.25 in | Product Depth US | 12.25 in |
| Product Height US | 12.5 in | Cable Length | 5 ft |

Additional Information

| | | | |
|----------------|-----|-------------------------------|-----|
| RoHS Compliant | Yes | Product Environmental Profile | Yes |
|----------------|-----|-------------------------------|-----|

Technical Information

| | | | |
|-----------------|-----|---------------------------|--------|
| Jacket Material | PVC | Operating Temperature Min | -10 °C |
|-----------------|-----|---------------------------|--------|

| | | | |
|-----------------------------|-------|------------|--------|
| Category Performance Rating | Cat5e | Wire Gauge | 24 AWG |
|-----------------------------|-------|------------|--------|

| | | | |
|------------------|---------------------------|-----------------------|--------------|
| Storage Humidity | 0-90% RH (Non-Condensing) | Plating Specification | 50 µ in Gold |
|------------------|---------------------------|-----------------------|--------------|

| | | | |
|--------------------|-------------|-------------|---------|
| Jacket Application | Riser Rated | Bend Radius | 0.86 in |
|--------------------|-------------|-------------|---------|

| | | | |
|---------------------|------------|-------------------|----------------|
| Shielded/Unshielded | Unshielded | Termination Style | Pre-Terminated |
|---------------------|------------|-------------------|----------------|

| | | | |
|---------------------|----------|---------------------------|-------|
| Conductor Stranding | Stranded | Operating Temperature Max | 60 °C |
|---------------------|----------|---------------------------|-------|

| | | | |
|---------------|----------|----------------|----------|
| Jacket Rating | CM Rated | Cable Diameter | 0.215 in |
|---------------|----------|----------------|----------|

| | | | |
|-------|--------------------|-----------------------|-----------|
| Braid | Non-braided Wiring | Operating Temperature | -10°-60°C |
|-------|--------------------|-----------------------|-----------|

| | | | |
|--------------------|---------------------------|--------------------|--------|
| Operating Humidity | 0-90% RH (Non-Condensing) | Conductor Material | Copper |
|--------------------|---------------------------|--------------------|--------|

| | | | |
|---------|---------|---------------------|--------------|
| Voltage | 300.0 V | Storage Temperature | -40° - 60° C |
|---------|---------|---------------------|--------------|
