



Ortronics  
**EZ Patch™ Flat Pack Clarity CAT6 5FT, 12 Pack, Black**  
Part No. EZFPM605Q12-00



The EZ Patch Flat Pack is an innovative addition to the EZ Patch series, allowing a 12 or 24-pack of cords to be distributed from flat plastic packaging, which is ideal for patch panel applications. Available in CAT6 & CAT6A

## Features & Benefits

**Bulk packaging:** Reduces installation time and packaging waste. No dealing with individual bags or zip ties.

**No cord memory:** Packs are laid out flat in a bundle

**Plastic packaging:** Ideal for data center applications that do not allow cardboard

**Light weight design:** Installers can easily carry the bag over their shoulder.

**Easy tear perforation strips:** Tears at each end allow for quick connection or easy removal of cords.

**Cable management:** Bag can be used as a fishing mechanism to route a bundle through a vertical manager.

**Packaged in 12 or 24 packs:** Quantities ideal for patch panel applications.

## Specifications

### General Info

Product Line	Ortronics	Color	Black
UPC Number	662875031512	Country Of Origin	Mexico
Application Sector	Commercial, Industrial	Warranty Type	5-Year
Type	Copper Patch Cord		

### Dimensions

Product Length US	5.0 FT	Cable Length	5 ft
-------------------	--------	--------------	------

### Additional Information

Product Environmental Profile Yes

---

## Technical Information

---

Jacket Material	PVC	Operating Temperature Min	-10 °C
Category Performance Rating	Cat6	Wire Gauge	24 AWG
Storage Humidity	0-90% RH (Non-Condensing)	Plating Specification	50 µ in Gold
Jacket Application	Riser Rated	Bend Radius	0.88 in
Shielded/Unshielded	Unshielded	Termination Style	Pre-Terminated
Conductor Stranding	Stranded	Operating Temperature Max	60 °C
Jacket Rating	CM Rated	Cable Diameter	0.22 in
Braid	Non-braided Wiring	Operating Temperature	-10°-60°C
Operating Humidity	0-90% RH (Non-Condensing)	Conductor Material	Copper
Voltage	300.0 V	Storage Temperature	-40° - 60° C

---