



The EZ Patch Flat Pack is an innovative addition to the EZ Patch series, allowing a 12 or 24-pack of cords to be distributed from flat plastic packaging, which is ideal for patch panel applications. Available in CAT6 & CAT6A

## Features & Benefits

**Bulk packaging:** Reduces installation time and packaging waste. No dealing with individual bags or zip ties.

**No cord memory:** Packs are laid out flat in a bundle

**Plastic packaging:** Ideal for data center applications that do not allow cardboard

**Light weight design:** Installers can easily carry the bag over their shoulder.

**Easy tear perforation strips:** Tears at each end allow for quick connection or easy removal of cords.

**Cable management:** Bag can be used as a fishing mechanism to route a bundle through a vertical manager.

**Packaged in 12 or 24 packs:** Quantities ideal for patch panel applications.

## Specifications

### General Info

|                    |                        |                   |        |
|--------------------|------------------------|-------------------|--------|
| Product Line       | Ortronics              | Color             | Orange |
| UPC Number         | 662875032052           | Country Of Origin | Mexico |
| Application Sector | Commercial, Industrial | Warranty Type     | 5-Year |
| Type               | Copper Patch Cord      |                   |        |

### Dimensions

|                   |        |              |      |
|-------------------|--------|--------------|------|
| Product Length US | 9.0 FT | Cable Length | 9 ft |
|-------------------|--------|--------------|------|

### Additional Information

Product Environmental Profile Yes

### Technical Information

|                 |     |                           |        |
|-----------------|-----|---------------------------|--------|
| Jacket Material | PVC | Operating Temperature Min | -10 °C |
|-----------------|-----|---------------------------|--------|

|                             |                           |                           |                |
|-----------------------------|---------------------------|---------------------------|----------------|
| Category Performance Rating | Cat6a                     | Wire Gauge                | 26 AWG         |
| Storage Humidity            | 0-90% RH (Non-Condensing) | Plating Specification     | 50 µ in Gold   |
| Jacket Application          | Riser Rated               | Bend Radius               | 0.932 in       |
| Shielded/Unshielded         | Unshielded                | Termination Style         | Pre-Terminated |
| Conductor Stranding         | Stranded                  | Operating Temperature Max | 60 °C          |
| Jacket Rating               | CM Rated                  | Cable Diameter            | 0.233 in       |
| Braid                       | Non-braided Wiring        | Operating Temperature     | -10°-60°C      |
| Operating Humidity          | 0-90% RH (Non-Condensing) | Conductor Material        | Copper         |
| Voltage                     | 300.0 V                   | Storage Temperature       | -40° - 60° C   |