



Ortronics
EZ Patch™ Flat Pack Reduced Diameter CAT6 3ft, 24 Pack, Black
Part No. EZFPR603Q24-00



"The EZ Patch™ Flat Pack is an innovative addition to the EZ Patch series, allowing 12 or 24 pack cords to be distributed from flat plastic packaging, which is ideal for patch panel applications or installations on the go.

Features & Benefits

Bulk packaging: Reduces installation time and packaging waste. No dealing with individual bags or zip ties.

No cord memory: Packs are laid out flat in a bundle

Plastic packaging: Ideal for data center applications that do not allow cardboard

Light weight design: Installers can easily carry the bag over their shoulder.

Easy tear perforation strips: Tears at each end allow for quick connection or easy removal of cords.

Cable management: Bag can be used as a fishing mechanism to route a bundle through a vertical manager.

Packaged in 12 or 24 packs: Quantities ideal for patch panel applications.

Specifications

General Info

| | | | |
|--------------------|------------------------|-------------------|--------|
| Product Line | Ortronics | Color | Black |
| UPC Number | 662875008354 | Country Of Origin | Mexico |
| Application Sector | Commercial, Industrial | Warranty Type | 5-Year |
| Type | Copper Patch Cord | | |

Dimensions

| | | | |
|-------------------|--------|--------------|------|
| Product Length US | 3.0 FT | Cable Length | 3 ft |
|-------------------|--------|--------------|------|

Additional Information

| | | | |
|----------------|-----|-------------------------------|-----|
| RoHS Compliant | Yes | Product Environmental Profile | Yes |
|----------------|-----|-------------------------------|-----|

Technical Information

| | | | |
|-----------------------------|---------------------------|---------------------------|----------------|
| Jacket Material | PVC | Operating Temperature Min | -10 °C |
| Category Performance Rating | Cat6 | Wire Gauge | 28 AWG |
| Storage Humidity | 0-90% RH (Non-Condensing) | Plating Specification | 50 µ in Gold |
| Jacket Application | Riser Rated | Bend Radius | 0.15 in |
| Shielded/Unshielded | Unshielded | Termination Style | Pre-Terminated |
| Conductor Stranding | Stranded | Operating Temperature Max | 60 °C |
| Jacket Rating | CMR Rated | Cable Diameter | 0.6 in |
| Braid | Non-braided Wiring | Operating Temperature | -10°-60°C |
| Operating Humidity | 0-90% RH (Non-Condensing) | Conductor Material | Copper |
| Voltage | 300.0 V | Storage Temperature | -40° - 60° C |
