



100GBase-LR4 QSFP28 Compatible Transceiver, SMF, 1295nm-1309nm, 10km, LC Duplex, DDM, C-Temp



Features & Benefits

- Guaranteed Compatible: In System tested in over 90 OEM switches, routers and servers.
- 99.98% Reliability Rate: Functionally, optically and environmentally tested to exact specifications.
- Industry Leading Lifetime Warranty: For more information by product line, visit our Warranty page.
- 98% On-Time Delivery Rate: Extensive inventory guarantees same day shipping.
- Full Service Technical Support: Call, chat, email or meet for expert optical connectivity support.

Specifications

General Info

| | | | |
|-------------------|-------------|---------------|--------------|
| Product Line | Ortronics | UPC Number | 662875063827 |
| Country Of Origin | China | Warranty Type | Lifetime |
| Type | Transceiver | | |

Dimensions

| | | | |
|-------------------|----------|------------------|-----------|
| Product Width US | 18.35 mm | Product Depth US | 125.35 mm |
| Product Height US | 8.5 mm | | |

Technical Information

| | | | |
|---------------------------|-------------|---------------------------|--------|
| Fiber Optic Cable Type | Single-Mode | Max Distance Support | 10 km |
| Operating Temperature Min | 0 °C | Operating Temperature Max | 70 °C |
| Connector Type | LC Duplex | Form Factor | QSFP28 |