



6' Plugmold Multioutlet System with 12 single outlets

## Features & Benefits

Steel Raceway. Provides superior strength for any dry location installation.

Available in Ivory ScuffCoat or gray baked enamel finish. The durable ScuffCoat provides a durable, scratch-resistant finish while the gray baked enamel compliments the décor or can be painted.

Single-and-dual-gang boxes. Wire devices into the raceway system or protect a Plugmold® strip with a surge or GFCI device.

Single, alternating circuit, and isolated ground receptacles. Meets virtually any job requirement.

Snapicoil harnesses of prewired receptacles in 48' and 50'. Eliminates multiple splicing, speeding up installation on long runs.

Customization available. All products can be modified to accommodate virtually any application.

Compact, low profile appearance. Requires minimal space.

Full range of fittings. Provides a complete wiring solution.

Factory wired Plugmold® sections available in 3', 5', and 6' lengths with 15A receptacles installed in cover. Ideal for short runs requiring additional outlets in electrically busy areas.

Choice of receptacle spacing. Center spacing between receptacles of 6", 9", 12", and 18".

Snapicoil harnesses offer a choice of receptacle spacing. Center spacing between receptacles of 12", 18" and 30".

This product meets the material restrictions of RoHS.

## Specifications

### General Info

Product Line	Wiremold	UPC Number	786776091861
Country Of Origin	United States	Number of Receptacles	12

cULus Listed Base & Blank Cover: File E4376  
Guide RJBT. Multioutlet Assemblies: File E15191  
Guide PVGT. Fittings: File E41751  
Guide RJPR. Base & Blank Cover & Plugmold Series w/Snapicoil Haarness: Meets Article 386 of NEC. Meets Section 12-3032 of CEC. cULus Listed Raceway: File E4376  
Guide RJBT. Fittings: File E41751  
Guide RJPR. Base & Black Cover: Meets Article 386 of NEC. Meets Section 12-600 of CEC.

Application Sector

Commercial

Standard

Type

Plugmold

#### Dimensions

Product Width US

1.3 in

Product Weight US

3.78 lb

Product Depth US

0.75 in

Product Length US

1.3 in

#### Listing Agencies / 3rd Party Agencies

cULus ListingNumber

E15191

cULus Listed

Yes

#### Trade Programs

USMCA

Yes

#### Additional Information

RoHS Compliant

Yes

Product Environmental Profile Yes

#### Technical Information

Amperage

15 A

Enclosure Type

Steel

Voltage

125.0 V

Environmental Conditions

Dry interior locations