


Legrand keyed LC fiber solutions provide a simple and convenient way to physically prevent the user from making an unauthorized connection by blocking access to specific optical ports, whether they are at a workstation outlet or in a telecommunications room or data center. This is particularly important for government, finance, military and other facilities where multiple networks having different security level access requirements may be co-located.



## Features & Benefits

**Unique Key and Color Options:** Up to thirteen unique keying options/colors for a wide range of network security systems, easy identification and network management.

**Various Footprint Options:** Keyed workstation adapter modules are available for TracJack® and High Density Jack (HDJ) style Face plates and surface mount boxes for complete system design flexibility.

**Keyed front or Rear:** Keyed LC adapters have the option to be keyed in the front only (user's side) or on both sides (user's and technician's) depending on the security requirements. Internal keying feature prevents tampering

**Compatibility:** All Legrand keyed LC fiber products are engineered to be compatible with other Legrand products to provide an end to end, data center to desktop solution.

## Specifications

### General Info

Product Line	Ortronics	Color	Aqua
UPC Number	662875027782	Country Of Origin	Mexico
Application Sector	Commercial	Warranty Type	5-Year
Type	Adapter Panel		

### Dimensions

Product Width US	4.19 in	Product Depth US	0.66 in
Product Height US	1.24 in		

### Technical Information

Fiber Optic Cable Type	OM3, OM4	Compatibility	M4/HDFP
Number of Ports	12	Simplex/Duplex	Duplex
Number of Fibers	12	Number of Fibers	12 Fibers
Connector 2	Non-Keyed Rose	Connector 1	Keyed Rose