



Wattstopper
HS Card Key Card Key Switch, Line Voltage, 120/277VAC, 50/60Hz, White
Part No. HS-150-W



The HS Series Card Key Switch turns electrical circuits on or off when a card key or HS-FOB Key Fob is inserted or removed from its slot.

Features & Benefits

Collection consolidated to white option

Line and low voltage models

Facilitates energy savings in hotels, motels and boarding houses

Optional key fob for rooms that do not use a card key

Room key activated master switch for hotel guest room lighting

30-second egress time

Backlit card key slot for visibility in darkened rooms

Specifications

General Info

Product Line	Wattstopper	Color	White
Finish	Glossy	UPC Number	754182920747
Country Of Origin	China	Switch Type	Card Key
Number of Switches	1	Application Sector	Commercial, Hospitality
Standard	UL, RoHS	Warranty Type	5-Year
Type	Switch		

Dimensions

Product Width US	2.96 in	Product Weight US	4.7 oz
------------------	---------	-------------------	--------

Product Volume US	23.7 cu in	Product Depth US	1.7 in
-------------------	------------	------------------	--------

Product Height US	4.7 in
-------------------	--------

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Operating Temperature Min	32 °F	Load Rating	1200 W @ 277 VAC, 1800 W @ 120 VAC
---------------------------	-------	-------------	------------------------------------

Compatibility	HS-FOB	Has Battery	No
---------------	--------	-------------	----

Operating Temperature Max	104 °F	Number of Buttons	0
---------------------------	--------	-------------------	---

Input Voltage	120/277 VAC	Indoor/Outdoor	Indoor
---------------	-------------	----------------	--------

Mounting Type	J-Box	Operating Temperature	32°-104°F
---------------	-------	-----------------------	-----------

Operating Humidity	5-95% RH (Non-Condensing)	Wire Connection Type	Flying Leads
--------------------	---------------------------	----------------------	--------------

Engraving Type	Icon with Text	Storage Temperature	23° - 176° F, -5° - 80° C
----------------	----------------	---------------------	---------------------------
