



Provides whole house audio and intercom.

Features & Benefits

- | | |
|--|--|
| 12-Port T568A/Universal Wiring | 1 AU7396 Single Source 4 Zone Distribution Module |
| 1 AU1004-WH Flush Mount Single Source Input | 4 AU7394-WH lyriQ Classic Standard Performance Keypad Volume Control |
| 4 MS3650 3000 Series 6.5inch In-Ceiling Speakers (pairs) | 1 IC1000 Broadcast Intercom Main Module |
| 4 IC1004-WH Broadcast Intercom Room Stations | 1 F7601 Broadcast Intercom Door Chime Module |
| 1 IC1001 Audio Interrupt Module | 1: F7596-OB Broadcast Intercom Door Station |
| 1 PW1060 24v, 2.5 Amp Power Supply | 1 PW7725 12v, 2.5Amp Power Supply |
| 1 WP1208-WH Three Gang Decorator Wall Plate | 1 WP1205-WH Single Gang Decorator Wall Plate |
| 1 F7425 Dual Head IR Emitter | 1 AU1060 lyriQ Dual Head IR Emitter |

Specifications

General Info

| | | | |
|-------------------|-------|--------------------|--------------|
| Product Line | On-Q | UPC Number | 804428050605 |
| Country Of Origin | China | Application Sector | Residential |

Additional Information

| | |
|----------------|-----|
| RoHS Compliant | Yes |
|----------------|-----|