



Pass and Seymour
Isolated Ground TVSS Quad Receptacle, Blue
Part No. IG420HBLSP



Isolated Ground Hospital Grade TVSS Quad Receptacle, 20A 125V,

Features & Benefits

Rugged nylon face and body withstands impacts and hard use.

Built-in wire stripping gauge.

Outward-facing ground terminals make handling up to four straight or angled plugs easy and convenient.

Heavy-duty, phosphor bronze contacts.

Shielding walls guard against live-circuit-to-ground shorts.

Split circuit break-off tabs.

UL and CSA listed.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	Blue
UPC Number	785007125726	Country Of Origin	Mexico
Application Sector	Commercial	Standard	UL1449, UL498: ANSI/IEEE C62.41 (Formerly IEEE 587), ANSI/IEEE C62.45 Installation Categories "A" (Ring Wave) "B" (Unidirectional Impulse).

Technical Information

Number of Wires	3	Temperature Rating	-40° - 65° C
Amperage	20 A	Number of Poles	Double Pole

Wire Size

14 - 12 AWG

Environmental Conditions

Flammability: UL94 V2 and
UL94-5 VA
