

Turnlok® Single Receptacle 3-Wire 15A 277V Isolated Ground



## Features & Benefits

Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.

Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.

IG symbol and Isolated Ground markings for easy identification and circuit delineation.

One-piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.

Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.

Side and external screw-pressure-plate back wire capability. Accepts #14-#10 AWG.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Orange
Finish	Matte	UPC Number	785007647600
Country Of Origin	Mexico	Receptacle Type	Locking
Number of Receptacles	1	Application Sector	Industrial
Standard	UL Listed	Type	Isolated Ground

### Dimensions

Product Width US	1.437 in	Product Depth US	4.03 in
Product Height US	1.203 in		

---

## Listing Agencies / 3rd Party Agencies

---

CSA Listed	Yes	cULus Listed	Yes
------------	-----	--------------	-----

---

CSA File Number	16063
-----------------	-------

---

## Technical Information

---

Phase	Three	Number of Wires	3
-------	-------	-----------------	---

---

Amperage	15 A	Number of Poles	Double Pole
----------	------	-----------------	-------------

---