



Wiremold
Rack Mount 120V/15A/6 front O/L /lighted switch/6' cord
Part No. J60B0B



Six front outlets, lighted switch, 15A, 6' (1.8m) cord.
Receptacle center-to-center 1 1/2" (38mm).

Features & Benefits

Six front 20A outlets, 6' (1.8m) cord. Receptacle center-to-center 1 1/2" (38mm).

Specifications

General Info

Product Line	Wiremold	UPC Number	786776043860
Country Of Origin	Mexico	Receptacle Type	Simplex
Number of Receptacles	6	Application Sector	Commercial
Standard	cULus Recognized: File E66421, Guide XBYS2 XUHT2 VZCA2	Type	PIOC

Dimensions

Product Width US	1.75 in	Product Weight US	3.0 lb
Product Depth US	2.57 in	Product Length US	19.0 in

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Phase	Single	Amperage	15 A
Enclosure Type	Steel	Mounting Type	Rack Mounting
Voltage	125.0 V	Environmental Conditions	Dry interior locations
