

Juniper JNP-QSFP-40G-LR4 Compatible 40GBase-LR4 QSFP+ Transceiver (SMF, 1271nm-1331nm, 10km, LC Duplex, DDM, C-Temp)



Features & Benefits

Guaranteed Compatible: In System tested in over 90 OEM switches, routers and servers.

99.98% Reliability Rate: Functionally, optically and environmentally tested to exact specifications.

Industry Leading Lifetime Warranty: For more information by product line, visit our Warranty page.

98% On-Time Delivery Rate: Extensive inventory guarantees same day shipping.

Full Service Technical Support: Call, chat, email or meet for expert optical connectivity support.

Specifications

General Info

| | | | |
|-------------------|-------------|---------------|--------------|
| Product Line | Ortronics | UPC Number | 662875078340 |
| Country Of Origin | China | Warranty Type | Lifetime |
| Type | Transceiver | | |

Dimensions

| | | | |
|-------------------|----------|------------------|---------|
| Product Width US | 18.35 mm | Product Depth US | 72.0 mm |
| Product Height US | 8.5 mm | | |

Technical Information

| | | | |
|---------------------------|-------------|---------------------------|-------|
| Fiber Optic Cable Type | Single-Mode | Max Distance Support | 10 km |
| Operating Temperature Min | 0 °C | Operating Temperature Max | 70 °C |
| Connector Type | LC Duplex | | |