



KT2J jacks, available in CAT6A, CAT6 and CAT5E, represent the next generation of keystone termination. These jacks utilize an installer friendly lacing cap termination. Termination tool supplied with every carton of 20 or bulk pack of 25.

Features & Benefits

Rear loading: Preferred mounting for panels.

Icon compatible, C5e marking on jack face: Supports 606 designation requirements.

Free termination tool in each carton of 20 jacks: Convenient no extra termination tool required.

RoHS compliant: Lead free.

Easy to follow universal wiring label: Quick and user-friendly, eliminates confusion.

Lacing Cap Design: No punch tool required, quick termination and installation time.

Always Ready for Install: Each package of jacks includes 1 standard lacing cap termination tool (Compatible with any HDJ or KT2 jacks).

Enhanced ergonomics: Optional high durability metal, lacing cap termination tool makes install easier, improving bulk installation and sustainability. Part Number: HDJHCT

Replacement plastic lacing cap termination tools, part number: HDJPCT-4PK

Specifications

General Info

Product Line	Ortronics	Color	Red
UPC Number	662875016908	Country Of Origin	Mexico
Application Sector	Commercial, Industrial	Standard	ANSI/TIA-568-C.2, UL 1863, IEEE 802.3af / 802.3at and Proposed 802.3bt Type 3 and Type 4, FCC part 68 Subpart F, IEC-603-7 compliant
Warranty Type	5-Year	Type	Jack

Dimensions

Product Width US	0.56 in	Product Depth US	1.23 in
Product Height US	0.63 in		

Additional Information

RoHS Compliant Yes

Technical Information

Wire Gauge 22 AWG Termination Style Lacing Cap

Connector Type RJ-45 IDC Wire Gauge 22-26 AWG

Impedance 100 Ohm
