



Category 6 Keystone jack, 8-position, 180 degree exit, icon compatible, T568A/B wiring, Fog White , individually packaged. Keystone, KT2J jacks and modules feature New installer friendly lacing cap termination with free termination tool in every carton. The keystone footprint allows flexibility in installation scheduling because its rear insertion into the faceplate allows the technician to complete the termination before and during the construction process.

Features & Benefits

Rear loading: Preferred mounting for panels.

Icon compatible, C5e marking on jack face: Supports 606 designation requirements.

Free termination tool in each carton of 20 jacks: Convenient no extra termination tool required.

RoHS compliant: Lead free.

Easy to follow universal wiring label: Quick and user-friendly, eliminates confusion.

Lacing Cap Design: No punch tool required, quick termination and installation time.

Always Ready for Install: Each package of jacks includes 1 standard lacing cap termination tool (Compatible with any HDJ or KT2 jacks).

Enhanced ergonomics: Optional high durability metal, lacing cap termination tool makes install easier, improving bulk installation and sustainability. Part Number: HDJHCT

Replacement plastic lacing cap termination tools, part number: HDJPCT-4PK

Specifications

General Info

Product Line	Ortronics	Color	Fog White
UPC Number	662875697862	Country Of Origin	Mexico
Application Sector	Commercial, Industrial	Standard	TIA-568.2-D, UL 1863, IEEE 802.3af / 802.3at and 802.3bt Type 3 and Type 4, FCC part 68 Subpart F, IEC-603-7 compliant
Warranty Type	5-Year	Type	Jack

Dimensions

Product Width US	0.56 in	Product Depth US	1.23 in
------------------	---------	------------------	---------

Product Height US	0.63 in
-------------------	---------

Additional Information

RoHS Compliant	Yes	Product Environmental Profile	Yes
----------------	-----	-------------------------------	-----

Technical Information

Compatibility	TechChoice Keystone	Wire Gauge	22 AWG
---------------	---------------------	------------	--------

Termination Style	Lacing Cap	Connector Type	RJ-45
-------------------	------------	----------------	-------

IDC Wire Gauge	22-26 AWG	Impedance	100 Ohm
----------------	-----------	-----------	---------
