



Turnlok® Receptacle 3-Wire 20A 3-Phase 480V

Features & Benefits

Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.

One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.

Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.

Accepts #14 - #10 AWG.

Face color coding by voltage facilitates locating and mating of proper devices.

Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.

Side and external screw-pressure-plate back wire capability.

Specifications

General Info

| | | | |
|--------------------|----------------|-------------------|--------|
| Product Line | Pass & Seymour | Color | Black |
| UPC Number | 785007122053 | Country Of Origin | Mexico |
| Application Sector | Commercial | Standard | UL 498 |

Dimensions

| | | | |
|-------------------|---------|------------------|---------|
| Product Width US | 1.61 in | Product Depth US | 1.19 in |
| Product Height US | 2.29 in | | |

Additional Information

| | |
|-------------------------------|-----|
| Product Environmental Profile | Yes |
|-------------------------------|-----|

Technical Information

| | | | |
|-----------|-------------|-----------------|---------|
| Phase | Three | Number of Wires | 3 |
| Amperage | 20 A | Number of Poles | 3-Way |
| Wire Size | 18 - 10 AWG | Voltage | 480.0 V |
