



Turnlok® Single Receptacle 4-Wire 20A 3-Phase 480V

## Features & Benefits

Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.

One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.

Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.

.032 inch thick, brass, triple-wipe power contacts for lasting retention.

Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.

Side and external screw-pressure-plate back wire capability.

## Specifications

### General Info

|                    |                        |                       |              |
|--------------------|------------------------|-----------------------|--------------|
| Product Line       | Pass & Seymour         | Color                 | Black        |
| Finish             | Matte                  | UPC Number            | 785007162059 |
| Country Of Origin  | Mexico                 | Number of Receptacles | 1            |
| Application Sector | Commercial, Industrial | Standard              | UL 498       |
| Type               | Outlet                 |                       |              |

### Dimensions

|                   |         |                  |         |
|-------------------|---------|------------------|---------|
| Product Width US  | 1.61 in | Product Depth US | 1.19 in |
| Product Height US | 2.29 in |                  |         |

---

## Listing Agencies / 3rd Party Agencies

---

|                     |        |              |     |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | 140596 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

---

## Additional Information

---

|                               |     |
|-------------------------------|-----|
| Product Environmental Profile | Yes |
|-------------------------------|-----|

---

## Technical Information

---

|          |      |                 |             |
|----------|------|-----------------|-------------|
| Amperage | 20 A | Number of Poles | Double Pole |
|----------|------|-----------------|-------------|

---

|           |       |                |        |
|-----------|-------|----------------|--------|
| Wire Size | 4 AWG | Indoor/Outdoor | Indoor |
|-----------|-------|----------------|--------|

---