

Turnlok® Flanged Outlet, 20A 347Vs Canadian, L24-20R



Features & Benefits

Interior components constructed of high-grade brass material for physical and electrical integrity. High-impact thermoplastic housing withstands on-the-job abuse.

Ratings and NEMA configurations are clearly visible on flange face, for fast I.D. while in use.

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
UPC Number	785007170030	Country Of Origin	Mexico
Application Sector	Industrial	Standard	CSA C22.2 No. 42

Dimensions

Product Width US	2.87 in	Product Depth US	1.34 in
------------------	---------	------------------	---------

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	CSA File Number	16063
------------	-----	-----------------	-------

Technical Information

Number of Wires	3	Amperage	20 A
Number of Poles	Double Pole	Wire Size	12 - 8 AWG

Environmental Conditions Flammability: UL94 V2: Operating
Temperature: Maximum continuous +115°C,
minimum -40°C without impact
