



Infinium M4 Cassettes are part of a complete fiber solution. When combined with matched Infinium Trunks and Infinium Patch Cable Assemblies the solution can enable industry leading pre-terminated performance and universal polarity for simple, fast and consistent and simplified installation. Compatible with Infinium HD-E Rack Mount Fiber Enclosure with M4 Drawer Face.

Features & Benefits

High Density: 12 or 24-fiber cassette compatible with Infinium HD M4 Enclosures

Fiber Type: Supports either Single-mode OS2 or Multimode Infinium Ultra fiber

LC adapter with internal shutter: Ensures eye safety by blocking laser light when the connector is removed. Automatic shutter requires no manual handling. Compatible with LC connectors, keeps the interior clean, and allows visible light to pass through.

Infinium Core: Low Loss System with Infinium Core Trunks and Patch Cords: Single-mode channel loss: 2.1 dB, return loss: 49 dB. Multimode channel loss: 2.5 dB, return loss: 19 dB.

Versatile Installation: Infinium Modular Panel enables mixed media installations

Polarization: Universal

Infinium Ultra: Ultra Low Loss System with Infinium Ultra Trunks and Patch Cords: Single-mode channel loss: 1.2 dB, return loss: 49 dB. Multimode channel loss: 1.0 dB, return loss: 19 dB.

Specifications

General Info

Product Line	Ortronics	Color	Aqua
UPC Number	662875031086	Country Of Origin	Mexico
Application Sector	Commercial	Standard	TIA-568-C.3
Warranty Type	5-Year	Type	Cassette

Dimensions

Product Width US	4.24 in	Product Depth US	4.77 in
Product Height US	1.14 in		

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Fiber Optic Cable Type	OM4	Compatibility	HDFP, LM4
------------------------	-----	---------------	-----------

Number of Ports	24	Simplex/Duplex	Duplex
-----------------	----	----------------	--------

Single/Multimode	Multimode	Performance Level/Tier	Infinium Ultra
------------------	-----------	------------------------	----------------
