



**Wattstopper**  
**DLM Dual cable connector for LMFC fixture integrated**  
Part No. LMFC-2RJ



The LMFC-xRJ provides fixture connectivity to the DLM local network via a single- or dual-port RJ45 wiring whip connector. The dual-port is best for daisy chaining multiple fixtures together. Each DLM local network can support up to 64 loads.

## Features & Benefits

Separate single- or dual-port RJ45 connector mounts on fixture housing, and provides connectivity to DLM local network

## Specifications

### General Info

Product Line	Wattstopper	Color	White
UPC Number	754182939015	Country Of Origin	China
Product Series	LMFC	Features	Flame Retardant, Impact Resistant, UV Grade
Installation Location	Fixture	Works With	DLM Fixture Controller
Application Sector	Commercial	Standard	UL, cUL, RoHS
Warranty Type	5-Year	Type	Interface

### Dimensions

Product Width US	1.5 in	Product Weight US	0.13 lb
Product Volume US	2.9 cu in	Product Depth US	0.8 in
Product Height US	2.4 in		

### Additional Information

RoHS Compliant	Yes
----------------	-----

---

## Technical Information

---

Operating Temperature Min 32 °F

Number of Connections 2

---

Operating Temperature Max 158 °F

Indoor/Outdoor Indoor

---

Mounting Type Snap-in

Operating Temperature 0°-70°C, 32°-158°F

---

Operating Humidity 5-95% RH (Non-Condensing)

---