



Infinium LM8 Cassettes are designed to enable Base 8 architecture and be part of a complete fiber solution. When combined with matched Infinium Trunks and Infinium Patch Cable Assemblies the solution enables industry leading preterminated performance and universal polarity for simple, fast and consistent and simplified installation. Compatible with Infinium HD Rack Mount Fiber Enclosure with LM8 Drawer Face.

Features & Benefits

Ultra Low Loss System	Optimized for 8-fiber transceivers and transmission technologies
100% fiber utilization for 8-fiber transceiver systems	Cable harnesses match common port counts on network devices
Flexibility for easy migration to 40G/100G/400G networks	

Specifications

General Info

Product Line	Ortronics	Color	Aqua
UPC Number	662875031147	Country Of Origin	Mexico
Application Sector	Commercial	Standard	TIA-568-C.3
Warranty Type	5-Year	Type	Cassette

Dimensions

Product Width US	2.75 in	Product Depth US	3.56 in
Product Height US	0.84 in		

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Fiber Optic Cable Type	OM4	Compatibility	HDJ, Infinium
Number of Ports	8	Simplex/Duplex	Duplex
Single/Multimode	Multimode	Performance Level/Tier	Infinium Ultra