



Wattstopper  
**LARGE NETWORK ENCLOSURE w/1NB-ROUTER 8-PORT SWITCH**  
Part No. LMNC-1-8



The LMNC is a surface-mount NEMA1-rated enclosure with DIN rails for mounting DLM network components. Comes with hinged cover and provided empty (LMNC-MT) or with 1-9 installed routers. Based on the catalog number suffix, a specific number of NB-ROUTERS and an NB-SWITCH can be installed in the panel and pre-wired to a power supply. Two single outlets are provided on the power supply, one for connecting an LMJA-8xxx-SM plug-in power supply, and a convenience outlet for a laptop or other technician required components.

## Features & Benefits

NEMA1-rated enclosure	DIN rail mounting for easy installation or removal of LMJA-8xxx-SM (ordered separately)
Includes selection of pre-wired NB-ROUTERS and NB-SWITCH	Single termination point for one 120VAC circuit to power all devices
Power supply with two 120V outlets for Network Controller power and laptop or other set up tools	

## Specifications

### General Info

Product Line	Wattstopper	Color	Gray
Finish	Glossy, Painted	UPC Number	754182943807
Country Of Origin	United States	Product Series	LMNC
Included	1 Router, 8 Network Ports, Data Cables, DIN Rails, Hinged Door, Power Supply, Power Wiring	Number of Knockouts	1
Application Sector	Commercial	Standard	UL, ANSI 61
Warranty Type	5-Year	Type	Enclosure

### Dimensions

Product Width US	16.0 in	Product Depth US	8.5 in
------------------	---------	------------------	--------

---

Product Height US 20.0 in

Knockout Size

1 in

---

### Technical Information

---

Compatibility DLM Wired

Power Supply

120 - 24VAC

---

Gauge 14

Enclosure Type

NEMA 1, Network

---

Configuration With Router and Switch

Input Voltage

120 VAC

---

Line Frequency 50 Hz, 60 Hz

Cable Entry

Knockout

---

Mounting Type Screw Mount

Mounting

Wall

---