



**Wattstopper**  
**NEMA1-Rated Small Enclosure for DLM Network Controller/Raccess**  
Part No. LMNC-ENC1



The LMNC-ENC1 is a surface-mount NEMA1-rated enclosure with a DIN rail for mounting one LMJA-8xxx-SM Network Controller with a removable cover. The conduit entrances and enclosure sections for high voltage (Class 1) and low voltage (Class 2) wiring are completely separated.

## Features & Benefits

NEMA1-rated enclosure	Compatible with LMJA-8xxx-SM, LMBR-650, Network switches and Router.
Shown with LMJA-8xxx-SM installed	Isolated Class 1 and Class 2 wiring
DIN rail mounting for easy installation or removal of Network Controller	

## Specifications

### General Info

Product Line	Wattstopper	Color	Black, Gray
Finish	Galvannealed	UPC Number	754182944903
Country Of Origin	China	Product Series	LMNC
Features	Isolated Class 1 and Class 2 Wiring	Included	2 Duplex Grounded Receptacles, Cover, DIN Rails
Number of Knockouts	8	Application Sector	Commercial
Standard	UL	Warranty Type	5-Year
Type	Enclosure		

### Dimensions

Product Width US	16.0 in	Product Weight US	12.2 lb
------------------	---------	-------------------	---------

---

Product Volume US	902.2 cu in	Product Depth US	5.375 in
-------------------	-------------	------------------	----------

---

Product Height US	10.5 in	Knockout Size	1/2 in, 3/4 in
-------------------	---------	---------------	----------------

---

### Additional Information

---

RoHS Compliant	Yes
----------------	-----

---

### Technical Information

---

Compatibility	DLM Wired	Gauge	16
---------------	-----------	-------	----

---

Enclosure Type	NEMA 1, Network	Configuration	With Receptacles
----------------	-----------------	---------------	------------------

---

Input Voltage	120 VAC	Line Frequency	50 Hz, 60 Hz
---------------	---------	----------------	--------------

---

Cable Entry	Knockout	Mounting Type	Screw Mount, Surface
-------------	----------	---------------	----------------------

---

Mounting	Wall
----------	------

---