



Wattstopper
RJ45 Cables, 75 ft, plenum rated, Green
Part No. LMRJ-P75



LMRJ Series cables connect Digital Lighting Management (DLM) components without the need for tools or point-to-point discrete wiring. Cables are pre-terminated with industry standard RJ45 connectors compatible with any RJ45 port on DLM components. LMRJ cables utilize B to B wiring.

Features & Benefits

Pre-terminated LMRJ cables for DLM local networks in lengths up to 100 feet

UL and cUL listed and labeled

Wattstopper LM-MSTP wire required for wired segment networks.

This wire is not needed for wireless DLM networks using the wireless bridge (LMBC-600)

Standard green color and markings for DLM provide easy identification of LMRJ cables in plenum

Cables and wire available in a choice of colors for use in exposed locations

LMRJ cables available in plenum and non-plenum rating

Specifications

General Info

| | | | |
|--------------------|--------------|-------------------|-------------------------|
| Product Line | Wattstopper | Color | Green |
| UPC Number | 754182939350 | Country Of Origin | China |
| Product Series | LMRJ | Jacket Color | Green with Black Stripe |
| Application Sector | Commercial | Standard | UL, cUL, PEP |
| Warranty Type | 5-Year | Type | Cable |

Dimensions

| | | | |
|-------------------|---------|-------------------|-------------|
| Product Weight US | 1.65 lb | Product Volume US | 270.0 cu in |
| Product Depth US | 0.5 in | Product Height US | 0.6 in |

| | | | |
|-------------------|----------|--------------|-------|
| Product Length US | 900.0 in | Cable Length | 75 ft |
|-------------------|----------|--------------|-------|

Technical Information

| | | | |
|-----------------|-----|-----------------------------|-------|
| Jacket Material | PVC | Category Performance Rating | Cat5e |
|-----------------|-----|-----------------------------|-------|

| | | | |
|------------|--------|--------------------|--------------|
| Wire Gauge | 24 AWG | Jacket Application | Plenum Rated |
|------------|--------|--------------------|--------------|

| | | | |
|---------------------|------------|-------------------|----------------|
| Shielded/Unshielded | Unshielded | Termination Style | Pre-Terminated |
|---------------------|------------|-------------------|----------------|

| | | | |
|-----------|----------------|------------|------------------|
| Conductor | 4-Pair Twisted | Cable Type | Booted, Snagless |
|-----------|----------------|------------|------------------|

| | | | |
|---------------|-----------|--------------------|-------|
| Jacket Rating | FT6 Rated | Temperature Rating | 75° C |
|---------------|-----------|--------------------|-------|

| | | | |
|----------------|--------|----------------|--------|
| Cable Diameter | 0.2 in | Indoor/Outdoor | Indoor |
|----------------|--------|----------------|--------|

| | | | |
|---------------------|--------------------------------------|--|--|
| Insulation Material | FEP (Fluorinated Ethylene Propylene) | | |
|---------------------|--------------------------------------|--|--|
