




**Wattstopper**  
**Discontinued - DLM Pre-Engraved Wall Switch, 3-Button w/IR, ON/OFF w/Arrows, Grey**  
 Part No. LMSW-103-G-ENG2



LMSW-100 Series Digital Wall Switches are low voltage devices for energy-saving manual on/ off control of one or more loads from one or more locations. They are part of a Digital Lighting Management (DLM) system and can control any load(s) connected to DLM room controllers.

## Features & Benefits

### 2-Button Wall Switch

LMSW-100 Series Digital Wall Switches are low voltage devices for energy-saving manual on/ off control of one or more loads from one or more locations

They are part of a Digital Lighting Management (DLM) system and can control any load(s) connected to DLM room controllers

Low voltage pushbutton switches for control of multiple loads

Each button can control individual or multiple loads, or one scene

Plug to other components using Cat 5e cable and RJ45 connectors eliminating wiring errors

Customizable buttons with LED status indicators

IR transceiver for wireless configuration and remote control

Plug n' Go automatic configuration and Push n' Learn for personalization

## Specifications

### General Info

Product Line	Wattstopper	Color	Gray
Finish	Glossy	UPC Number	754182946129
Country Of Origin	China	Product Series	LMSW
Switch Type	Push	Number of Switches	3
Application Sector	Commercial	Standard	UL, cUL, FCC part 15, RoHS
Warranty Type	5-Year	Type	Switch

---

## Dimensions

---

Product Width US	1.8 in	Product Weight US	0.1861 lb
Product Volume US	19.845 cu in	Product Depth US	1.6 in
Product Height US	4.2 in		

---

## Technical Information

---

Operating Temperature Min	0 °C	Compatibility	DLM Wired
Has Battery	No	Operating Temperature Max	55 °C
Number of Buttons	3	Number of Rockers	0
Topology	Free Topology	Input Voltage	24 VDC
Indoor/Outdoor	Indoor	Mounting Type	J-Box
Current Draw	5 mA	Operating Temperature	0°-55°C, 32°-131°F
Operating Humidity	5-95% RH (Non-Condensing)	Wire Connection Type	RJ-45
Engraving Type	Text	Storage Temperature	23° - 176° F, -5° - 80° C

---