



Incandescent Slide Dimmer, 1000watt 3way Preset, Black

Features & Benefits

Ergonomic design and solid, quality feel combine for smooth, easy operation and precise Electromagnetic and radio-frequency interference protection built in. control.

Sleek, sculpted contemporary design. No dirt-catching crevices.

Tough, impact-resistant thermoplastic housing makes it a perfect choice for new home construction. Matching, unbreakable TradeMaster wall plate available for all models.

Preset ON/OFF switch automatically returns controlled lights to preset level without readjusting dimmer setting.

Exclusive, screw-pressure-plate back wire terminals save time, space and money. Designed for 12 and 14 gauge wire, stranded or solid. No-wire-lead design eliminates wire nuts.

Superior heat management.

No derating on 600W units.

Patented Snap-In Light Module (sold separately) transforms the dimmer into an illuminated dimmer.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Replaced by Part Number	LS603PBK
Color	Black	UPC Number	785007045543
Country Of Origin	China	Application Sector	Commercial, Residential
Standard	UL/CSA Listed	Type	Dimmer

Listing Agencies / 3rd Party Agencies

cULus ListingNumber

95219

cULus Listed

Yes

Technical Information

Operating Cycles

100000

Number of Poles

Single Pole

Wattage

1000 W
