



Pass and Seymour
Discontinued - LS Series Incandescent Slide Dimmer, Ivory
Part No. LS600I

Incandescent Slide Dimmer, Preset 600W



Features & Benefits

Ergonomic design and solid, quality feel combine for smooth, easy operation and precise control.

Sleek, sculpted contemporary design. No dirt-catching crevices.

Exclusive, screw-pressure-plate back wire terminals save time, space and money. Designed for 12 and 14 gauge wire, stranded or solid. No-wire-lead design eliminates wire nuts.

No derating on 600W units.

For covering patents, see www.legrand.us/patents.

Electromagnetic and radio-frequency interference protection built in.

Tough, impact-resistant thermoplastic housing makes it a perfect choice for new home construction. Matching, unbreakable TradeMaster wall plate available for all models.

Superior heat management.

Patented Snap-In Light Module (sold separately) transforms the dimmer into an illuminated dimmer.

Specifications

General Info

| | | | |
|--------------------|----------------|-------------------|-----------|
| Product Line | Pass & Seymour | Color | Ivory |
| UPC Number | 785007157901 | Country Of Origin | China |
| Application Sector | Residential | Standard | UL Listed |
| Type | Dimmer | | |

Listing Agencies / 3rd Party Agencies

| | | | |
|---------------------|-------|--------------|-----|
| cULus ListingNumber | 95219 | cULus Listed | Yes |
|---------------------|-------|--------------|-----|

Technical Information

| | | | |
|------------------|--------|-----------------|-------------|
| Operating Cycles | 100000 | Number of Poles | Single Pole |
|------------------|--------|-----------------|-------------|

| | |
|---------|-------|
| Wattage | 600 W |
|---------|-------|
