



Pass and Seymour  
LS Series CFL/LED/Incandescent Single Pole Slide Dimmer, Non-Preset, Black  
Part No. LSCL450BK



Works with select dimmable CFL/LED or incandescent lighting loads and features a sleek, sculpted ergonomic design for smooth, easy operation and precise control.

## Features & Benefits

CFL/LED dimmable bulb compatible (except for 0-10V LED drivers)	Works with dimmable CFL/LED or Incandescent lighting loads at 450W CFL/LED & 700W Incandescent
Built-in electromagnetic and radio-frequency interference protection	No dirt-catching crevices
Tough, impact-resistant thermoplastic housing makes it a perfect choice for new home construction. Matching, unbreakable TradeMaster wall plates available for all models	Preset ON/OFF switch automatically returns controlled lights to preset level without re-adjusting dimmer setting
Exclusive, screw-pressure-plate back wire terminals save time, space and money. Designed for 12 and 14 gauge wire, stranded or solid. No-wire-lead design eliminates wire nuts	Superior heat management
Patented Snap-In Light Module (sold separately) transforms the dimmer into an illuminated dimmer	Rating: 450W LED & CFL: 700W Incandescent: 120VAC 60Hz

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Black
Finish	Matte	UPC Number	785007040463
Country Of Origin	China	Product Series	Trademaster
Features	Low-End Trim (Dim Range)	Switch Type	Single Pole, Slider
Number of Switches	1	Application Sector	Residential
Standard	cULus, RoHS	Warranty Type	Limited Lifetime Warranty

---

Type	Dimmer
------	--------

---

## Dimensions

---

Product Width US	1.74 in	Product Depth US	1.28 in
------------------	---------	------------------	---------

---

Product Height US	4.19 in
-------------------	---------

---

## Technical Information

---

Preset	No	Load Rating	120V 4.5A 450W (CFL), 120V 4.5A 450W (LED), 120V 700W (Halogen), 120V 700W (Incandescent)
--------	----	-------------	---

---

Dimming Compatibility	Forward Phase	Frequency Rating	60 Hz
-----------------------	---------------	------------------	-------

---

Number of Poles	Single Pole	Wire Size	#14 - #10 AWG
-----------------	-------------	-----------	---------------

---

Requires Neutral Wire	No	Indoor/Outdoor	Indoor
-----------------------	----	----------------	--------

---

Mounting Type	Wall Box	Wire Connection Type	Screw Terminals
---------------	----------	----------------------	-----------------

---

Voltage	120 VAC	Load Type	CFL, Halogen, Incandescent, LED
---------	---------	-----------	---------------------------------

---

Environmental Conditions	Humidity: Less than 95% non condensing
--------------------------	--

---