



Ortronics  
Q-Series Cassette 12 Fiber, Single-Mode Fiber, Type A  
Part No. M2LCD12-09



Momentum 2 modular fiber optic pre-terminated cassettes provide the fastest method of structured cabling deployment: plug it in and you're ready to go. Factory-terminated and tested cassettes guarantee field performance.

## Features & Benefits

Factory-terminated and tested cassettes guarantee field performance.

Data label printed with insertion loss value for each port adhered to the cassette housing.

Available in Single, Multi-Mode, 12 fiber or 24 fiber ports

## Specifications

### General Info

Product Line	Ortronics	Color	Blue
UPC Number	662875608141	Country Of Origin	Taiwan, Province Of China
Application Sector	Commercial	Standard	TIA-568-C.3
Warranty Type	5-Year	Type	Cassette

### Dimensions

Product Width US	5.13 in	Product Depth US	4.77 in
Product Height US	1.03 in		

### Additional Information

RoHS Compliant	Yes	Product Environmental Profile	Yes
----------------	-----	-------------------------------	-----

### Technical Information

---

Fiber Optic Cable Type	OS2	Number of Ports	12
Single/Multimode	Single-Mode	Performance Level/Tier	Infinium Core

---