

Infinium M4 pre-terminated cassettes with method B provide rapid deployment and have a flipped polarity inside the modules, which use key-up to key-up MPO adapters and allows for straight through patching. The rugged metal housing offers additional durability and includes a built-in internal bend limiting feature to assure optimum optical performance.



Features & Benefits

| | |
|---|--|
| Fully Compatible with Infinium INFC Enclosures | 4 Cassettes Fit into 1U |
| Front Adapter Housing Colors Follow TIA/EIA-568.3-D Suggested Color Identification Scheme | Each cassette has a data label with insertion loss value for each port |

Specifications

General Info

| | | | |
|--------------------|--------------|-------------------|-------------|
| Product Line | Ortronics | Color | Aqua |
| UPC Number | 662875001041 | Country Of Origin | China |
| Application Sector | Commercial | Standard | TIA-568-C.3 |
| Warranty Type | 5-Year | Type | Cassette |

Dimensions

| | | | |
|-------------------|---------|------------------|---------|
| Product Width US | 3.45 in | Product Depth US | 4.77 in |
| Product Height US | 1.14 in | | |

Additional Information

| | |
|----------------|-----|
| RoHS Compliant | Yes |
|----------------|-----|

Technical Information

| | | | |
|------------------------|---------------|---------------------------|-----------|
| Fiber Optic Cable Type | OS2 | Operating Temperature Min | 0 °C |
| Compatibility | HDFM | Number of Ports | 12 |
| Simplex/Duplex | Duplex | Operating Temperature Max | 70 °C |
| Return Loss | 55 dB | Single/Multimode | Multimode |
| Performance Level/Tier | Infinium Core | Operating Temperature | 0°-70°C |
| Storage Temperature | -40° - 70° C | | |