



The 24-fiber OM4 M4 Cassettes are designed to be used with the Infinium HD Enclosures and support MPO to LC Quad adapter 8-fiber connectivity, offering versatile installation and swift deployment. The housing of the cassettes offer additional durability and integrated bend limiting considerations to assure optimum optical performance. The Base 8 configuration of this cassette matches the fiber utilization of most transceivers, providing for 100% fiber utilization. This makes these cassettes a perfect match for Ethernet transmission ranging from 40G to 400G.

Features & Benefits

High Density: 12 or 24-fiber cassette compatible with Infinium HD M4 Enclosures

Versatile Installation: Infinium Modular Panel enables mixed media installations

Fiber Type: Supports either Single-mode OS2 or Multimode Infinium Ultra fiber

Specifications

General Info

Product Line	Ortronics	UPC Number	662875026068
Country Of Origin	China	Application Sector	Commercial
Standard	TIA-568-C.3	Type	Cassette

Dimensions

Product Width US	4.24 in
------------------	---------

Additional Information

RoHS Compliant	Yes
----------------	-----