



Infinium M4 Splice Cassettes enable industry leading performance, fast field termination, and provide cable management within the housing. The Splice Cassettes are designed for use with Single-Mode (OS2) or Multimode (OM4/OM5) Fiber, Houses 12-24 fibers and are available in LC Duplex or LC Quad port configurations. Compatible with Infinium HD-E Rack Mount Fiber Enclosure with M4 Drawer Face.

## Features & Benefits

Flexible Install: Mount from the front or the rear of an enclosure or panel

Installation Convenience: Do all splicing and managing work outside the enclosure

Clear Top: Enables fast and easy fault identification

Compact: These Splice cassettes provide a very compact splicing solution

Front or Rear Mounting: Simplify installation by mounting from the front or rear of the enclosure panel

Flexible Install: Mount from the front or rear of an enclosure or panel

Patented Splice Management: Simplify Splicing and fiber management outside of the cassette with the removable fiber splice manager

## Specifications

### General Info

Product Line	Ortronics	Color	Aqua
UPC Number	662875025580	Country Of Origin	China
Included	(12 or 24) Fiber Pigtails, Adapter Panel, Protective Dust Caps, Splice Management Tray, Splice Protection Sleeves	Application Sector	Commercial
Standard	TIA-568-C.3	Warranty Type	5-Year
Type	Cassette		

### Dimensions

Product Width US	3.45 in	Product Depth US	4.77 in
Product Height US	1.14 in		

---

## Additional Information

---

RoHS Compliant      Yes

---

## Technical Information

---

Fiber Optic Cable Type	OM4	Compatibility	Infinium, M4
Number of Ports	24	Simplex/Duplex	Duplex
Single/Multimode	Multimode	Performance Level/Tier	Infinium Quantum

---