



Infinium M4 Splice Cassettes enable industry leading performance, fast field termination, and provide cable management within the housing. The Splice Cassettes are designed for use with Single-Mode (OS2) or Multimode (OM4/OM5) Fiber, Houses 12-24 fibers and are available in LC Duplex or LC Quad port configurations. Compatible with Infinium HD-E Rack Mount Fiber Enclosure with M4 Drawer Face.

## Features & Benefits

|  |   |
|--|---|
| Flexible Install: Mount from the front or the rear of an enclosure or panel  | Installation Convenience: Do all splicing and managing work outside the enclosure |
| Clear Top: Enables fast and easy fault identification  | Compact: These Splice cassettes provide a very compact splicing solution          |
| Front or Rear Mounting: Simplify installation by mounting from the front or rear of the enclosure panel                            | Flexible Install: Mount from the front or rear of an enclosure or panel           |
| Patented Splice Management: Simplify Splicing and fiber management outside of the cassette with the removable fiber splice manager |   |

## Specifications

### General Info

|                    |              |                   |        |
|--------------------|--------------|-------------------|--------|
| Product Line       | Ortronics    | Color             | Aqua   |
| UPC Number         | 662875027126 | Country Of Origin | China  |
| Application Sector | Commercial   | Warranty Type     | 5-Year |
| Type               | Cassette     |                   |        |

### Dimensions

|                   |         |                  |         |
|-------------------|---------|------------------|---------|
| Product Width US  | 3.45 in | Product Depth US | 4.77 in |
| Product Height US | 1.14 in |                  |         |

### Technical Information

---

|                        |           |                        |                |
|------------------------|-----------|------------------------|----------------|
| Fiber Optic Cable Type | OM4       | Compatibility          | Infinium, M4   |
| Number of Ports        | 24        | Simplex/Duplex         | Duplex         |
| Single/Multimode       | Multimode | Performance Level/Tier | Infinium Ultra |

---