



This M4 Splice Cassette enables fast, field termination and provides cable management within the housing. The M4 Splice Cassette is designed for use with Single-Mode OS2 fiber, houses 12 fibers, and provides SC APC Duplex ports. This cassette supports fusion splicing of individual fibers, with heat shrinks, pigtail slack and cable slack managed within the cassette. This eliminates the need for individual splice trays or housings, as well as allowing splicing to be done away from the rack housing in a suitable workspace as needed. The design of the cassette allows it to be easily mounted from either the front or the rear of an enclosure or panel. Individual fibers within the cassette may be accessed without disturbing the other fibers in the housing. -

Features & Benefits

Mounts from either the front or rear of the enclosure or panel

Tier 1 performance characteristics for insertion and return loss

Specifications

General Info

Product Line	Ortronics	Color	Blue
UPC Number	662875011873	Country Of Origin	Mexico
Application Sector	Commercial	Standard	TIA-568-C.3
Warranty Type	5-Year	Type	Cassette

Dimensions

Product Width US	4.19 in	Product Depth US	6.15 in
Product Height US	1.24 in		

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Fiber Optic Cable Type	OS2	Compatibility	M4
Number of Ports	12	Simplex/Duplex	Duplex
Return Loss	65 dB	Single/Multimode	Single-Mode
Performance Level/Tier	Infinium Core		