



Wiremold
Plug-In Outlet Center Unit / 120V/20A/6 O/L /lighted switch/6' cord/Computer Grade Surge
Part No. M620BZLS



Perma Power computer grade surge protection. Six outlets, lighted switch, durable putty white aluminum housing, 20A. 6' (1.8m) 12/3 SJT putty white cord with NEMA 5-20 plug. Length 18" (457mm). Snap-on, slide-off mounting.

Features & Benefits

Perma Power computer grade surge protection. Six outlets, lighted switch, durable putty white aluminum housing, 20A. 15' (4.6m) 12/3 SJT putty white cord with NEMA5-20 plug. Length 18" (457mm). Snap-on, slide-off mounting.

Specifications

General Info

Product Line	Wiremold	UPC Number	786776524666
Country Of Origin	Mexico	Application Sector	Commercial, Residential
Standard	cULus Listed: File E66421 Guide XYBS XUHT VZCA	Type	PIOC

Dimensions

Product Width US	18.0 in	Product Weight US	4.0 lb
Product Height US	1.89 in	Product Length US	2.0 in

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E66421	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Phase	Single Stage	Connection	Cord-ended
Class	75	Amperage	20 A
Short Circuit Rating	36000 Amps [12000 Amps L-N 12000 Amps L-G 12000 Amps N-G]	Response Time	<1 ns

Mounting Type	Slide-off, Snap-on	Mounting	Yes
Type of Indicators	Light	Voltage	120.0 V
Environmental Conditions	Indoor, dry location		
