



## Wiremold

**Plug-In Outlet Center Unit / 120V/15A/6 O/L /remote lighted switch/15' cord/Computer Grade Surge**  
Part No. M6BZR-15



Perma Power computer grade surge protection. Six outlets, remote switch, durable putty white aluminum housing, 15A. 15' (4.6m) 14/3 SJT putty white cord with NEMA5-15 plug. Length 13 1/4" (337mm). Snap-on, slide-off mounting.

### Features & Benefits

Perma Power computer grade surge protection. Six outlets, remote switch, durable putty white aluminum housing, 15A. 15' (4.6m) 14/3 SJT putty white cord with NEMA5-15 plug. Length 13 1/4" (337mm). Snap-on, slide-off mounting.

### Specifications

#### General Info

Product Line	Wiremold	UPC Number	786776047752
Country Of Origin	Mexico	Application Sector	Commercial, Residential
Standard	cULus Listed: File E66421 Guide XYBS XUHT VZCA	Type	PIOC

#### Dimensions

Product Width US	13.75 in	Product Weight US	4.0 lb
Product Height US	1.89 in	Product Length US	2.0 in

#### Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E66421	cULus Listed	Yes
---------------------	--------	--------------	-----

#### Trade Programs

USMCA	Yes
-------	-----

#### Technical Information

Phase	Single Stage	Connection	Cord-ended
Class	75	Amperage	15 A

---

Short Circuit Rating	36000 Amps [12000 Amps L-N 12000 Amps L-G 12000 Amps N-G]	Response Time	<1 ns
Mounting Type	Snap-on, Slide-off	Mounting	Yes
Type of Indicators	Light	Voltage	120.0 V
Environmental Conditions	Indoor, dry location		

---