



Pass and Seymour
Discontinued - Midget Flanged Outlet - Black Face, Gray Flange
Part No. ML214

Midget Lock Flanged Outlet 2-Pole 3-Wire 15A 125A



Features & Benefits

Quality Materials, durability, and time-tested design

Wire Size: 18/3 thru 14/3 AWG Round cord (.23" - .52" Dia.)

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
UPC Number	785007124507	Country Of Origin	Mexico
Application Sector	Commercial, Industrial	Standard	UL Listed

Dimensions

Product Width US	2.06 in	Product Depth US	1.26 in
------------------	---------	------------------	---------

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes
------------	-----

Technical Information

Phase	Single	Number of Wires	3
Amperage	15 A	Number of Poles	Double Pole

Wire Size

18 - 14 AWG

Environmental Conditions

UL94 V2, Maximum
Continuous +75°C, minimum -
40°C without impact
