



Ortronics
MM20 Channel Rack, 16.25" deep, 7 ft, 45 RU, Square Hole Rails, Black
 Part No. MM2071638-B



The mighty mo 20 channel racks are designed to provide the greatest in cable management flexibility and efficiency. Honeycomb cutout sidewall allow for infinite cable pathways. The universal 3/8" square hole punch enables mounting of all standard cage nuts and OEM quick mount slides and rails. This creates the industries most versatile equipment rack system.

Features & Benefits

- Many option for all applications: 5 depths, square hole with rack unit fingers & hinged slam latch door, cage with rack unit fingers & snap-on covers, cage with hinged latches, and individual or tapped hole configurations
- Built-in top trough with waterfalls: Gives bend radius control and cable routing.
- Speed nuts included: Increases speed and ease of assembly, while adding extra strength to your rack-- Speednut eliminates the need for a second wrench.
- Large range of accessories
- Rack includes hardware kit, two packages of hook and loop D-style straps and 50 #12-24 equipment mounting screws: Do not have to purchase as separate items- money saving.
- Open channels top and bottom: Allows floor and ceiling access for horizontal distribution cables.
- Vertical management solutions: A solution for every application-cage with rack unit fingers & hinged slam latch door, cage with rack unit fingers & snap-on covers, cage with hinged latches, and individual cable management rings.
- Can be assembled as a 19" or 23" rack: No additional hardware required- no need to stock two sizes of racks.
- Easy Installation: Mighty Mo 20 Racks can assemble in less than 15 minutes/rack
- Cablofil® ready cable tray & runway brackets
- Honeycomb side rails designed to maximize the airflow of network equipment: Combined with baffles, manages intake and exhaust air creating cold aisle/hot aisle distribution from side vented equipment.

Specifications

General Info

Product Line	Ortronics	Color	Black
UPC Number	662875836506	Country Of Origin	United States
Application Sector	Commercial	Type	Rack

Dimensions

Product Width US	23.75 in	Product Weight US	38.67 lb
------------------	----------	-------------------	----------

Product Depth US	16.25 in	Product Height US	86.0 in
------------------	----------	-------------------	---------

Rack Depth	16.25 in
------------	----------

Additional Information

RoHS Compliant	Yes	Product Environmental Profile	Yes
----------------	-----	-------------------------------	-----

Technical Information

Rack Units	45	Static Load Capacity	2000 lb
------------	----	----------------------	---------
