



Mighty Mo 20 4-post adjustable racks allow all 4 mounting rails to be adjusted even after the rack has been fastened to the floor. Available in depths of 30", 36" & 42" depths in both square hole cage nut styles or threaded rails. Front and rear waterfalls allow for equipment patching and server patching. All styles of Mighty Mo 20 vertical managers can be mounted front or rear and airflow baffles can be mounted to manage the airflow of side breathing equipment.

Features & Benefits

Large selection of Channel and 4-Post racks	All 4 mounting rails to be adjusted even after the rack has been fastened to the floor
Front and rear waterfalls allow for equipment patching and server patching	Static capacity 2,000 lbs
Threaded hole and square hole punch available on all channel and 4 post racks	Deeper waterfall for increased cable capacity
Rack includes two packages of hook and loop D-style straps and 50 #12-24 cage nuts and screws, do not have to purchase as separate items; money saving	

Specifications

General Info

Product Line	Ortronics	UPC Number	662875948957
Country Of Origin	United States	Type	Rack

Dimensions

Product Width US	23.75 in	Product Weight US	55.17 lb
Product Depth US	40.0 in	Product Height US	86.0 in

Technical Information

Static Load Capacity	2000 lb
----------------------	---------