



The wire frame and rack unit finger design promotes efficient routing of patch cords between racks. Dual hinged slam latch doors allow easy access during moves, adds and changes. Supplied with four cable management spools to provide slack storage for fiber jumpers and twelve bend limiting clips to protect fiber entering the vertical manager.

Features & Benefits

- Accepts 180° Bend limiting clips for fiber access
- Bottom support to eliminate sag and step issues
- Clean aesthetic look
- Spring loaded actuator on handles for smooth opening and closing
- Left or right hinge and removable door.
- 2" deeper fingers for higher density networks
- Deeper vertical managers with up to 40% more room
- Strong flexible fingers
- Larger capacity, including longer finger sections

Specifications

General Info

Product Line	Ortronics	Color	Black
Finish	Powder Coat	UPC Number	662875216117
Country Of Origin	United States	Included	Mounting Hardware
Application Sector	Commercial	Warranty Type	5-Year
Type	Rack		

Dimensions

Product Width US	6.45 in	Product Weight US	49.77 lb
Product Depth US	15.0 in	Product Height US	77.0 in

Additional Information

Product Environmental Profile Yes

Technical Information

Compatibility Mighty Mo Rack Units 45

Seismic Tested No Mounting Vertical
