



Wattstopper MSTP Router for LI Controls BASRT-B-WS DIN mounting Part No. NB-ROUTER



The NB-ROUTER provides a connection point between a single Digital Lighting Management (DLM) segment network and an Ethernet LAN. The router has a rugged metal enclosure with an integral DIN rail mounting clip.

Features & Benefits

Routes one BACnet MS/TP Segment Network to BACnet IP

Simple configuration using a standard web browser

Compatible with DLM Network Controller or third party BACnet building automation systems

BACnet/IP or BACnet Ethernet connectivity

Specifications

General Info

Product Line	Wattstopper	Color	Gray
Finish	Painted	UPC Number	754182106189
Country Of Origin	United States	Product Series	NB
Installation Location	Enclosure, Wall	Application Sector	Commercial
Standard	IP30, RoHS, UL 508	Warranty Type	1-Year
Type	Network Router		

Dimensions

Product Width US	2.74 in	Product Weight US	1.0 lb
Product Height US	1.0 in	Product Length US	4.85 in

Additional Information

DesignLights Consortium Qualified System	Yes	Security	Yes
--	-----	----------	-----

Technical Information

Operating Temperature Min	32 °F	Compatibility	DLM Wired
Number of Connections	1	Power Supply	24 VDC/VAC
Operating Temperature Max	140 °F	Indicator	Network Status LED, Power LED
Connector Type	RJ-45, RS-485	Input Voltage	24 VDC/VAC
Indoor/Outdoor	Indoor	Mounting Type	DIN Rail
Operating Temperature	0°-60°C, 32°-140°F	Operating Humidity	10-95% RH (Non-Condensing)
Storage Temperature	-40° - 85° C		
