



Wiremold
Plug-In Outlet Center Unit / Polymeric/120V/15A/36 long/6 O/L /6' cord
 Part No. NM20-C3



Six (3 duplex) outlets, nonmetallic housing with ivory finish. 6' (1.8m) cord. Length 36" (915mm). Receptacle center-to-center 12" (305mm).

Features & Benefits

Six (3 duplex) outlets, nonmetallic housing with ivory finish. 6' (1.8m) cord. Length 36" (915mm). Receptacle center-to-center 12" (305mm).

Specifications

General Info

Product Line	Wiremold	UPC Number	786776520392
Country Of Origin	United States	Number of Receptacles	3

Application Sector	Commercial	Standard	cULus Listed Base & Blank Cover: File E90378 Guide RJBT. Multioutlet Assemblies: File E15191 Guide PVGT. Fittings: File E90377 GuideRJPR. Base & Blank Cover & Plugmold Series w/Snapcoil Harness: Meets Article 386 of NEC. Meets Section 12-3032 of CEC. Plugmold Wired Sections: Meets Article 380 of NEC. Meets Section 12-3032 of CEC.
--------------------	------------	----------	---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

Type	Plugmold
------	----------

Dimensions

Product Weight US	2.3 lb
-------------------	--------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E66421	cULus Listed	Yes
---------------------	--------	--------------	-----

Trade Programs

USMCA	Yes
-------	-----

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Amperage	15 A	Enclosure Type	Non-Metallic
Voltage	120.0 V	Environmental Conditions	Dry interior locations
