



Nuvo
Discontinued - 7-in Android PoE Touch Screen, Black
 Part No. NVP30BK



The Nuvo P30 Touch Screen (NV-P30-BK) is a seven inch Android tablet designed for convenient, complete, in-wall control of the Player Portfolio System. The P30 runs the Player Portfolio app and Spotify for seamless and unified control of your home audio allowing access to your favorite streaming services or music stored on networked devices. Connecting is simple, with a single RJ45 802.11af PoE cable.

While the Player Portfolio app offers aesthetic handheld control, providing an in-wall option allows fixed location control - especially convenient for muting or lowering volume quickly when there's a knock at the door, or allowing immediate access to preset source favorites without locating a phone or tablet.

Check out the [Player Portfolio mobile app](#).

Features & Benefits

Connects simply with a single RJ45 802.11af PoE cable

Convenient, complete, in-wall control of the Nuvo Player Portfolio system

Discreet and aesthetic design blends easily into a room's decor

Fully functioning tablet allows access to other apps, like Spotify, Pandora, and more

Runs the Player Portfolio app for seamless control of your home audio, including streaming services and music stored on networked devices

See what's playing control the entire house from one spot

Sleek, high contrast seven inch 1024 x 600 IPS capacitive touch screen.

Universal mounting plate. (* Streaming services subject to geographic availability. Service subscriptions may be required)

Specifications

General Info

Product Line	Nuvo	Replaced by Part Number	NVP30WH
Color	Black	UPC Number	701963859413
Country Of Origin	China	Application Sector	Residential

Standard
 FCC, CFR Title 47 Part 15, Subpart B, ICES-003,
 CISPR13, 55020 C-TICK, AS/NZS CISPR13,
 RoHS

Technical Information

Control	HA7000 Intuity Automation Control Module, or web devices, iOS, Android	Input	Supports up to 4 IP cameras
Amperage	350 mA	Monitor	Includes LCD touch screen
Wattage	12.95 W	Environmental Conditions	70% (relative humidity, non-condensing)
