


Q-Series OFP Standard Density Adapter Panels offer pass-through connections and front-loading access for Q-Series Enclosures. Compatible with Q-Series Rack Mount or Wall Mount Fiber Enclosures.



## Features & Benefits

Up to 72 LC fibers per RU

Available in, LC, SC, ST and blank styles

Made of durable polycarbonate

Zirconia ceramic sleeves for optimal performance

6, 8, 12 & 24 port panels

Color options available

## Specifications

### General Info

Product Line	Ortronics	Color	Aqua
UPC Number	662875968948	Country Of Origin	Mexico
Application Sector	Commercial	Warranty Type	5-Year
Type	Adapter Panel		

### Dimensions

Product Width US	5.12 in	Product Depth US	1.15 in
Product Height US	1.19 in		

### Technical Information

Fiber Optic Cable Type	OM3, OM4	Number of Ports	8
Simplex/Duplex	Duplex	Single/Multimode	Multimode