



Ortronics
6-LC (12 fibers) multimode aqua adapters with ceramic alignment sleeves
Part No. OFP-LCD12LC



The Ortronics OptiMo® OFP series adapter panels are used with our popular Q-Series modular fiber enclosures, offering great flexibility in structured cabling design. Front-removable adapter panels are available with LC, SC, ST, and MT-RJ adapters and feature options ideal for both single mode and multimode applications.

Features & Benefits

Up to 72 LC fibers per RU	Available in, LC, SC, ST and blank styles
Made of durable polycarbonate	Zirconia ceramic sleeves for optimal performance
6, 8, 12 & 24 port panels	Color options available

Specifications

General Info

Product Line	Ortronics	Color	Aqua
UPC Number	662875629856	Country Of Origin	Mexico
Application Sector	Commercial	Standard	RoHS compliant. Meets or exceeds TIA/EIA-568-C.3 requirements
Warranty Type	5-Year	Type	Adapter Panel

Dimensions

Product Width US	5.12 in	Product Depth US	1.15 in
Product Height US	1.19 in		

Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Fiber Optic Cable Type	OM3, OM4	Number of Ports	12
Simplex/Duplex	Duplex	Single/Multimode	Multimode
Number of Fibers	12 Fibers	Fiber Type	Multi-Mode

Form Factor

LC Duplex
